


## Tube Clamps with Elastomer Inlay Serie C



### Clamp-halves

#### Order codes:

Polypropylene – **RCPE**

Polyamide 6 – **RCNE**

If required, replace the standard indicator RCPE in the order code columns.

### Elastomer Inlay

#### Order code:


TPE 73° Shore – **EE\***

\*complete with clamp size and outside tube diameter

Clamp size Serie C	Tube O.D. mm	Clamp body	Order code Clamp body with elastomer inlay	Elastomer inlay
2	6.0	RCPE2X	RCPE206X	EE206/406X
	8.0		RCPE208X	EE208/408X
	10.0		RCPE210X	EE210/410X
	12.0		RCPE212X	EE212/412X
	12.7		RCPE212.7X	EE212.7/412.7X
	14.0		RCPE214X	EE214/414X
	15.0		RCPE215X	EE215/415X
	16.0		RCPE216X	EE216/416X
	17.2		RCPE217.2X	EE217.2/417.2X
	18.0		RCPE218X	EE218/418X
	19.0		RCPE219X	EE219/419X
3	20.0	RCPE3X	RCPE320X	EE320/620X
	21.3		RCPE321.3X	EE321.3/621.3X
	22.0		RCPE322X	EE322/622X
	23.0		RCPE323X	EE323/623X
	25.0		RCPE325X	EE325/625X
	26.9		RCPE326.9X	EE326.9/626.9X
	28.0		RCPE328X	EE328/628X
	30.0		RCPE330X	EE330/630X
	32.0		RCPE332X	EE332/632X
4	32.0	RCPE4X	RCPE432X	EE432X
	33.7		RCPE433.7X	EE433.7X
	35.0		RCPE435X	EE435X
	38.0		RCPE438X	EE438X
	40.0		RCPE440X	EE440X
	42.0		RCPE442X	EE442X
	45.5		RCPE445.5X	EE445.5X
	48.0		RCPE448X	EE448X
	51.0		RCPE451X	EE451X
	53.4		RCPE453.4	EE453.4X
	56.4		RCPE456.4X	EE456.4X
	60.3		RCPE460.3X	EE460.3X
5	57.0	RCPE5X	RCPE557X	EE557X
	60.3		RCPE560.3X	EE560.3X
	63.5		RCPE563.5X	EE563.5X
	65.0		RCPE565X	EE565X
	70.0		RCPE570X	EE570X
	73.0		RCPE573X	EE573X
	76.1		RCPE576.1X	EE576.1X

**Attention!** For clamps with elastomer inlay, the relation of diameter and size is not identical with the profile design or smooth design.

## Tube Clamps with Elastomer Inlay Serie C



### Clamp-halves

#### Order codes:

Polypropylene – **RCPE**

Polyamide 6 – **RCNE**

If required, replace the standard indicator RCPE in the order code columns.

### Elastomer Inlay

#### Order code:

TPE 73° Shore – **EE\***

\*complete with clamp size and outside tube diameter

Clamp size Serie C	Tube O.D. mm	Order code		Elastomer inlay
		Clamp body	Clamp body with elastomer inlay	
6	80.0	<b>RCPE6X</b>	<b>RCPE680X</b>	<b>EE680X</b>
	82.5		<b>RCPE682.5X</b>	<b>EE682.5X</b>
	88.9		<b>RCPE688.9X</b>	<b>EE688.9X</b>
	100.0		<b>RCPE6100X</b>	<b>EE6100X</b>
	101.6		<b>RCPE6101.6X</b>	<b>EE6101.6X</b>
7	101.6	<b>RCPE7X</b>	<b>RCPE7101.6X</b>	<b>EE7101.6X</b>
	108.0		<b>RCPE7108X</b>	<b>EE7108X</b>
	114.3		<b>RCPE7114.3X</b>	<b>EE7114.3X</b>
	127.0		<b>RCPE7127X</b>	<b>EE7127X</b>
	133.0		<b>RCPE7133X</b>	<b>EE7133X</b>

**Attention!** For clamps with elastomer inlay, the relation of diameter and size is not identical with the profile design or smooth design.